



FibrBoss Wall Mounting Fiber Optic Box, outdoor, 6 LC/APC adapters, with pre-installed pigtails

- Intended as a small patch and splice or fiber “hands-off” enclosure
- Environmentally secure housing for indoor or outdoor wall mounted application
- Accommodates field supplied flat or round drop cable inputs
- Cable retention brackets are integrated into the fiber management tray
- Splice protection sleeves are included to add customer convenience and efficiency

## Product Classification

<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	PB06
<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   North America

## General Specifications

<b>Application</b>	For cables with outer diameter up to 10 mm: each on both sides
<b>Cable Type</b>	Pigtails - Stranded
<b>Enclosure Color</b>	Beige
<b>Functionality</b>	Patching   Splicing
<b>Includes</b>	Splice protectors   Splice tray
<b>Interface Feature, input</b>	APC
<b>Interface, input</b>	LC
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Port, quantity</b>	6
<b>Splicing Capacity, maximum</b>	6

## Dimensions

<b>Depth</b>	60.96 mm   2.40 in
<b>Height</b>	121.92 mm   4.80 in
<b>Width</b>	162.56 mm   6.40 in

## Mechanical Specifications

<b>Access</b>	Front
<b>Enclosure Material Type</b>	LSZH thermoplastic
<b>Front Cover Type</b>	Hinged with lock
<b>Lock Type</b>	Padlock ready
<b>Mount Type</b>	Pedestal   Pole   Wall

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Insertion Loss, Terminal Connector, maximum</b>	0.20 dB
<b>Return Loss, Connector, minimum</b>	55 dB

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standard</b>	IEC 60529, IP65

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**

