

MX6-SPL6030-A-U7Z4



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit up, Putty white, 7 ft

Product Classification

Brand	OMX600®
Product Series	OMX
Product Type	Fiber entrance cabinet
Regional Availability	Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	299.72 mm 11.80 in
Height	2133.60 mm 84.00 in
Width	596.90 mm 23.50 in

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	Seismic rating, zone 4

General Specifications

Color	Putty white
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184

Mechanical Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Mount Type	Concrete floor

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification

