



XAGA™ FOSC™ A1 Fiber Optic Splice Closure, Heat Shrink Cable sealing, complete kit with one pre-installed 12-splice tray, with cable blocking

Product Classification

Product Type	In-line, round fiber closure
Regional Availability	Latin America North America
Product Series	XAGA FOSC
Product Brand	FOSC™ XAGA®

General Specifications

Splicing Type, Supported	Mechanical Single fusion
Color	Black
Network Area Type	Distribution
Package, quantity	1
Packaging Type	Box Carton
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink

Dimensions

Main Cable Diameter, maximum	25.00 mm
Diameter	134.62 mm 5.30 in
Length	711.20 mm 28.00 in
Weight	1.00 kg 2.20 lb

Mechanical Specifications

Cable Sealing Type	Heat shrink
Cable Ports, quantity	2
Closure Sealing Type	Wraparound sleeve
Closure Style	In-line
Material Type	Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space	Below ground Buried
----------------------------	-----------------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

