



FIST-GPS2 Fiber Panel for holding up to 6 GPST Patch/Splice Trays, unloaded, 3RU, 19 in, gray

Product Classification

Brand	FIST™
Product Series	FIST-GPS2
Product Type	Fiber patch/splice panel
Regional Availability	EMEA

Construction Materials

Finish	Powder coated
Material Type	Galvanized steel

Dimensions

Height	133.35 mm 5.25 in
Width	482.60 mm 19.00 in

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

General Specifications

Rack Units	3.0
Shelf Movement	Sliding
Application	Used in FIST-GR3-style frames only
Color	Gray
Color, front	Gray
Functionality	Patching Splicing
Growth Configuration	Unloaded
Includes	Mounting hardware
Package Quantity	1
Rack Type	EIA 19 in ETSI 600 mm

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

