



FIST-GPS2 Fiber Panel for holding up to 2 GPST Patch/Splice Trays, unloaded, 1RU, 19 in, gray

## Product Classification

<b>Brand</b>	FIST™
<b>Product Series</b>	FIST-GPS2
<b>Product Type</b>	Fiber patch/splice panel
<b>Regional Availability</b>	EMEA

## Construction Materials

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +45 °C (+23 °F to +113 °F)
<b>Relative Humidity</b>	Up to 93%, non-condensing
<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)

## General Specifications

<b>Rack Units</b>	1.0
<b>Shelf Movement</b>	Sliding
<b>Application</b>	Used in FIST-GR3-style frames only
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Functionality</b>	Patching   Splicing
<b>Growth Configuration</b>	Unloaded
<b>Includes</b>	Mounting hardware
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in   ETSI 600 mm

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

