

FIST-GPS2 Fiber Termination/Splice Panel, LC/APC, 3RU, with 6 trays, ETSI width, gray

Product Classification

Brand	FIST™
Product Series	FIST-GPS2
Product Type	Fiber patch/splice panel
Regional Availability	EMEA

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Galvanized steel

Dimensions

Height	133.35 mm 5.25 in
Width	531.00 mm 20.91 in

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

General Specifications

Rack Units	3.0
Shelf Movement	Sliding
Application	Used in FIST-GR3-style frames only
Color	Gray
Color, front	Gray
Functionality	Patching Splicing
Includes	Mounting hardware
Package Quantity	1
Rack Type	ETSI 600 mm

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

