



FIST-GSS2 Fiber Splice Panel, 3RU, 19 in, gray

Product Classification

Brand	FIST™
Product Series	FIST-GSS2
Product Type	Fiber splice panel
Regional Availability	EMEA

Construction Materials

Finish	Powder coated
Material Type	Galvanized steel

Dimensions

Height	133.35 mm 5.25 in
Width	482.60 mm 19.00 in

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

General Specifications

Rack Units	3.0
Shelf Movement	Sliding
Application	Used in FIST-GR3-style frames only
Color	Gray
Color, front	Gray
Functionality	Splicing
Includes	Mounting hardware
Package Quantity	1
Rack Type	EIA 19 in ETSI 600 mm

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

