

FOMS-FPS Fiber Termination/Splice Panel, 24 SC/UPC, singlemode, 1RU, 19 in, gray

Product Classification

Product Series	FOMS-FPS
Product Type	Fiber patch/splice panel
Regional Availability	EMEA

Construction Materials

Fiber Mode	Singlemode
Material Type	Ethylene-propylene (EP) Polyethylene terephthalate (PET)

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	1.0
Shelf Movement	Hinged
Color	Gray
Color, front	Gray
Functionality	Patching Splicing
Includes	Mounting hardware
Interface Feature, front	Standard
Interface, front	SC
Package Quantity	1
Rack Type	EIA 19 in EIA 23 in ETSI 600 mm
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

