

G2 ULL Multimode OM5 MPO-24 Distribution Module, 1x24F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



Product Classification

Portfolio	SYSTIMAX®
Brand	SYSTIMAX ULL
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM5, LazrSPEED® wideband
Total Fibers, quantity	24

Dimensions

Depth	113.28 mm 4.46 in
Height	24.64 mm 0.97 in
Width	95.00 mm 3.74 in

Environmental Specifications

Qualification Standards	TIA/EIA-568-C.3
Safety Standard	cUL US 1863

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Lime green
Adapters, quantity, front	12
Data Module Type	G2
Intelligence Type	iPatch® ready
Shuttered	No
Interface, rear	MPO Unpinned
Adapters, quantity, rear	1
Interface Feature, rear	Key up

Color, rear Lime green

Package Quantity 1

Optical Performance

Insertion Loss, maximum 0.35 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

