



High-Density Front-Loading Cable Manager Shallow, 15U

- Offers bend radius and mechanical protection
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords
- Suitable for Twisted Pair and Fiber Optic patch cords

Product Classification

Portfolio	CommScope®
Product Type	Cable management hardware
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	98.05 mm 3.86 in
Height	666.75 mm 26.25 in
Width	62.50 mm 2.46 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL

General Specifications

Color	Black
Rack Units	15
Finish	Smooth
Minimum Order Quantity	2
Ordering Note	Sold per piece with an MOQ of 2 pieces
Package Quantity	1

Mechanical Specifications

Material Type	Galvanized steel PA TPE
----------------------	-----------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

