

High-Density Front-Loading Cable Manager Shallow, 2U



- Offers bend radius and mechanical protection
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords
- Suitable for Twisted Pair and Fiber Optic patch cords

Product Classification

| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Cable management hardware |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|---------------|--------------------|
| Depth | 98.05 mm 3.86 in |
| Height | 88.90 mm 3.50 in |
| Width | 62.50 mm 2.46 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Safety Standard | cUL UL |

General Specifications

| | |
|-------------------------------|--|
| Color | Black |
| Rack Units | 2 |
| Finish | Smooth |
| Minimum Order Quantity | 8 |
| Ordering Note | Sold per piece with an MOQ of 8 pieces |
| Package Quantity | 1 |

Mechanical Specifications

| | |
|----------------------|-----------------------------|
| Material Type | Galvanized steel PA TPE |
|----------------------|-----------------------------|

Regulatory Compliance/Certifications

| | |
|-----------------|-----------------------|
| Agency | Classification |
| RoHS 2011/65/EU | Compliant |

