



IFDB Fiber Optic Wall Box with 4 SC/APC adapters, 1 preterminated 1x4 splitter

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

Product Classification

Product Type	Fiber wall box
Product Series	IFDB
Regional Availability	EMEA

General Specifications

Adapters, quantity	4
Color	Light gray
Functionality	Patching Splitting
Includes	Optical splitter (1)
Interface Feature, input	APC
Interface, input	SC
Package, quantity	12
Packaging Type	Bag Carton

Dimensions

Depth	49.00 mm 1.93 in
Height	216.00 mm 8.50 in
Width	126.00 mm 4.96 in

Mechanical Specifications

Front Cover Type	Screw-on
Material Type	Thermoplastic
Mount Type	Wall Floor

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space Indoor
Flammability Rating UL 94 V-0
Qualification Standard IEC 60529, IP30

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

