



## Rapid Fiber™ EFDT NID Wall Mounting Fiber Box, outdoor, 12 SC/APC, 8-way splitter

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

## Product Classification

<b>Brand</b>	Rapid Fiber™
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	EFDT
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Distribution Type</b>	1 x 8 splitter
<b>Enclosure Color</b>	Gray
<b>Functionality</b>	Patching   Splitting
<b>Interface Feature, input</b>	APC
<b>Interface, input</b>	SC
<b>Package, quantity</b>	8
<b>Packaging Type</b>	Box   Carton
<b>Port, quantity</b>	12
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Depth</b>	71.12 mm   2.80 in
<b>Height</b>	264.16 mm   10.40 in
<b>Width</b>	179.07 mm   7.05 in

## Mechanical Specifications

<b>Access</b>	Front
<b>Enclosure Material Type</b>	LSZH thermoplastic
<b>Front Cover Type</b>	Hinged with lock
<b>Mount Type</b>	Wall

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, Splitter, maximum</b>	11.0 dB
<b>Return Loss, Connector, minimum</b>	55 dB
<b>Wavelength Range</b>	1260–1650 nm

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>Qualification Standard</b>	IEC 60529, IP55   IEC 61753-1, category G

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

