



IWB Fiber Wall Box, 2-door, 24-ports, unloaded, no pigtails, 1 cable clamp

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Product Series	IWB
Product Type	Fiber wall box
Regional Availability	Asia EMEA

Construction Materials

Finish	Powder coated
Material Type	Steel

Dimensions

Depth	85.00 mm 3.35 in
Height	350.00 mm 13.78 in
Width	425.00 mm 16.73 in

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA type 12

General Specifications

Application	Patching Splicing
Color	Gray
Door, quantity	2
Growth Configuration	Unloaded
Package Quantity	1
Packaging Type	Bag Carton
Splice Trays Included, quantity	0
Splicing Type	Mass fusion

Mechanical Specifications

Cable Clamps, quantity	1
Cable Entry Location	Bottom right Top right
Front Door Type	Single hinged

Mount Type

Wall

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

