



IWB Fiber Wall Box, 2-door, 48-ports, unloaded, no pigtails, 1 cable clamp

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

## Product Classification

<b>Product Series</b>	IWB
<b>Product Type</b>	Fiber wall box
<b>Regional Availability</b>	Asia   EMEA

## Construction Materials

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Depth</b>	140.00 mm   5.51 in
<b>Height</b>	350.00 mm   13.78 in
<b>Width</b>	505.00 mm   19.88 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	NEMA type 12

## General Specifications

<b>Application</b>	Patching   Splicing
<b>Color</b>	Gray
<b>Door, quantity</b>	2
<b>Growth Configuration</b>	Unloaded
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Type</b>	Mass fusion

## Mechanical Specifications

<b>Cable Clamps, quantity</b>	1
<b>Cable Entry Location</b>	Bottom right   Top right
<b>Front Door Type</b>	Single hinged

**Mount Type**

Wall

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

