



G2 ULL 4x6 Singlemode Conversion Module, (4) MPO-12 unpinned ports rear, (6) MPO-8 pinned front

Product Classification

Portfolio	SYSTIMAX®
Brand	SYSTIMAX ULL
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.657.A2
Total Fibers, quantity	48

Dimensions

Depth	117.35 mm 4.62 in
Height	26.42 mm 1.04 in
Width	96.52 mm 3.80 in

Environmental Specifications

Safety Standard	cUL US 1863
------------------------	-------------

General Specifications

Interface, front	MPO
Total Ports, quantity, front	6
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	6
Data Module Type	Fiber Conversion Module
Shuttered	No
Interface, rear	MPO Unpinned
Adapters, quantity, rear	4
Interface Feature, rear	Key up
Color, rear	Blue
Package Quantity	1

Optical Performance

Insertion Loss, maximum 0.70 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

