



G2 ULL 4x6 Multimode OM5 WideBand Conversion Module, (2) MPO-24 unpinned ports rear, (6) MPO-8 pinned front

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	SYSTIMAX ULL
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OM5, LazrSPEED® wideband
<b>Total Fibers, quantity</b>	48

## Dimensions

<b>Depth</b>	117.35 mm   4.62 in
<b>Height</b>	26.42 mm   1.04 in
<b>Width</b>	96.52 mm   3.80 in

## Environmental Specifications

<b>Safety Standard</b>	cUL US 1863
------------------------	-------------

## General Specifications

<b>Interface, front</b>	MPO
<b>Total Ports, quantity, front</b>	6
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Lime green
<b>Adapters, quantity, front</b>	6
<b>Data Module Type</b>	Fiber Conversion Module
<b>Shuttered</b>	No
<b>Interface, rear</b>	MPO Unpinned
<b>Adapters, quantity, rear</b>	2
<b>Interface Feature, rear</b>	Key up
<b>Color, rear</b>	Lime green
<b>Package Quantity</b>	1

## Optical Performance

**Insertion Loss, maximum** 0.40 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

