



LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP BOD270A1

OBSOLETE

This product was discontinued on: February 1, 2019

Replaced By

CP-59091086-00

CP-5909 1 086-00

LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP OD270A1

Product Classification

Brand	LSA-PLUS®
Product Type	Overvoltage plug
Regional Availability	EMEA

Dimensions

Height	12.70 mm 0.50 in
Length	38.60 mm 1.52 in
Width	9.70 mm 0.38 in

Electrical Specifications

Capacitance	50.00 pF
Current Rating, maximum	90.00 mA
dc Resistance, maximum	1.00 ohm
Dielectric Strength	2 kV
Insulation Resistance, minimum	1000 MOhm
Safety Voltage Rating	270 V
Transmission Standard	DIN EN 60068-2-1 DIN EN 60068-2-2/3 DIN EN 60068-2-6 ITU-T K.12

Environmental Specifications

Environmental Space	Indoor
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Package Quantity 10
Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

