



LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP BI70A2

OBSOLETE

This product was discontinued on: **February 1, 2019**

Replaced By

CP-59091082-01

CP-5909 1 082-01

LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP I70A2

Product Classification

Brand	LSA-PLUS®
Product Type	Overvoltage plug
Regional Availability	EMEA

Dimensions

Height	12.70 mm 0.50 in
Length	38.60 mm 1.52 in
Width	9.70 mm 0.38 in

Electrical Specifications

Capacitance	50.00 pF
Current Rating, maximum	150.00 mA
dc Resistance, maximum	1.00 ohm
Dielectric Strength	2 kV
Safety Voltage Rating	70 V
Transmission Standard	DIN EN 60068-2-1 DIN EN 60068-2-2/3 DIN EN 60068-2-6 ITU-T K.12

Environmental Specifications

Environmental Space	Indoor
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Package Quantity	10
-------------------------	----

Packaging Type

Bag | Box

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

