

Copper Patch Panel, FLT Series, 1U, 48 port, staggered pattern, loaded with Cat6 SL jacks

OBSOLETE

This product was discontinued on: October 1, 2018

Replaced By

760237060
NPP-UDDM-SL-1U-48 Discrete Distribution Module Panel, Cat6, UTP, 1U, 48 port

Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6
Transmission Standard	ANSI/TIA-568-C.2 ISO/IEC 11801 Class E

General Specifications

Total Ports, quantity	48
Cable Type	Unshielded
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Package Quantity	1
Packaging Type	Bag Box
Rack Type	EIA 19 in
Rack Units	1.0

Mechanical Specifications

Panel Style	Straight
Material Type	High-impact, flame retardant, thermoplastic Steel
Panel Mounting	Flush

Termination Type IDC
Wiring T568A | T568B

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

