



IFDB Fiber Optic Wall Box with Universal splice holder for up to 4 mechanical or SMOUV splices

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

Product Classification

Product Type	Fiber wall box
Product Series	IFDB
Regional Availability	EMEA

General Specifications

Adapters, quantity	0
Color	Light gray
Functionality	Splicing
Package, quantity	20
Packaging Type	Bag Carton
Splice Tray Chip Type	Mechanical SMOUV
Splicing Capacity, maximum	4

Dimensions

Depth	35.00 mm 1.38 in
Height	80.00 mm 3.15 in
Width	80.00 mm 3.15 in

Mechanical Specifications

Front Cover Type	Screw-on
Material Type	Thermoplastic
Mount Type	Wall Floor

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Flammability Rating UL 94 V-0
Qualification Standard IEC 60529, IP30

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

