



EHD ULL 24 LC ribbon splice cassette, LazrSPEED OM4, Enhanced Method B, includes 2, FST-ACC006 mass fusion splice sleeves

Product Classification

Product Series EHD
Product Type Fiber cassette with pigtails

Construction Materials

Fiber Type OM4, LazrSPEED® 550

Dimensions

Depth 163.83 mm | 6.45 in
Height 11.43 mm | 0.45 in
Weight 0.45 kg | 1.00 lb
Width 169.67 mm | 6.68 in

Environmental Specifications

Safety Standard cUL US 1863

General Specifications

Interface, front LC
Adapters, quantity, front 24
Color, front Aqua
Interface Feature, front Standard
Package Quantity 1
Total Ports, quantity, front 24

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

FST-ACC006 — Fiber Optic Protective Splice Sleeve, 12f mass fusion, 1 package



Fiber Optic Protective Splice Sleeve, 12f mass fusion, 1 package

Product Classification

Product Type Fiber splice sleeve
Regional Availability North America

Environmental Specifications

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Package Quantity 1
Splicing Type Heat shrink, mass fusion

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

