



FMS Fiber Optic Termination/Splice Panel, 1U, 19 in, 48 LC/UPC, multimode, OM3, black

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Series</b>	FMS
<b>Product Type</b>	Fiber patch/splice panel
<b>Regional Availability</b>	Asia

## Construction Materials

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM3
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Depth</b>	320.00 mm   12.60 in
<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## General Specifications

<b>Rack Units</b>	1.0
<b>Shelf Movement</b>	Sliding
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Functionality</b>	Patching   Splicing
<b>Growth Configuration</b>	Fully loaded
<b>Includes</b>	Mounting hardware
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	LC
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Splice Trays Included, quantity</b>	2
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	48

## Mechanical Specifications

**Cable Exit Location**                      Rear, left side | Rear, right side

## Optical Performance

**Insertion Loss, maximum**            0.30 dB

**Return Loss, minimum**                20.0 dB

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

