



FMS Fiber Optic Termination/Splice Panel, 1U, 19 in, 24 LC/UPC, multimode, OM3, black

## Product Classification

|                              |                          |
|------------------------------|--------------------------|
| <b>Portfolio</b>             | NETCONNECT®              |
| <b>Product Series</b>        | FMS                      |
| <b>Product Type</b>          | Fiber patch/splice panel |
| <b>Regional Availability</b> | Asia                     |

## Construction Materials

|                      |               |
|----------------------|---------------|
| <b>Fiber Mode</b>    | Multimode     |
| <b>Fiber Type</b>    | OM3           |
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Depth</b>  | 320.00 mm   12.60 in |
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.60 mm   19.00 in |

## General Specifications

|                                        |                                  |
|----------------------------------------|----------------------------------|
| <b>Rack Units</b>                      | 1.0                              |
| <b>Shelf Movement</b>                  | Sliding                          |
| <b>Body Style</b>                      | Symmetrical                      |
| <b>Color</b>                           | Black                            |
| <b>Color, front</b>                    | Black                            |
| <b>Functionality</b>                   | Patching   Splicing              |
| <b>Growth Configuration</b>            | Partially loaded                 |
| <b>Includes</b>                        | Mounting hardware                |
| <b>Interface Feature, front</b>        | Standard                         |
| <b>Interface, front</b>                | LC                               |
| <b>Package Quantity</b>                | 1                                |
| <b>Rack Type</b>                       | EIA 19 in                        |
| <b>Splice Trays Included, quantity</b> | 2                                |
| <b>Splicing Type</b>                   | Heat shrink, single fiber fusion |
| <b>Total Ports, quantity</b>           | 24                               |

## Mechanical Specifications

**Cable Exit Location**                      Rear, left side | Rear, right side

## Optical Performance

**Insertion Loss, maximum**            0.30 dB

**Return Loss, minimum**                20.0 dB

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

