



FMS Fiber Optic Termination/Splice Panel, 2U, 19 in, 96 LC/UPC, multimode, OM3, black

Product Classification

Portfolio	NETCONNECT®
Product Series	FMS
Product Type	Fiber patch/splice panel
Regional Availability	Asia

Construction Materials

Fiber Mode	Multimode
Fiber Type	OM3
Finish	Powder coated
Material Type	Steel

Dimensions

Depth	320.00 mm 12.60 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	2.0
Shelf Movement	Sliding
Body Style	Symmetrical
Color	Black
Color, front	Black
Functionality	Patching Splicing
Growth Configuration	Fully loaded
Includes	Mounting hardware
Interface Feature, front	Standard
Interface, front	LC
Package Quantity	1
Rack Type	EIA 19 in
Splice Trays Included, quantity	4
Splicing Type	Heat shrink, single fiber fusion

Total Ports, quantity 96

Mechanical Specifications

Cable Exit Location Rear, left side | Rear, right side

Optical Performance

Insertion Loss, maximum 0.30 dB

Return Loss, minimum 20.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

