



FMS Fiber Optic Termination Panel, 1U, 19 in, 24 LC/UPC, multimode, OM3/OM4, black

Product Classification

| | |
|------------------------------|-------------------|
| Portfolio | NETCONNECT® |
| Product Series | FMS |
| Product Type | Fiber patch panel |
| Regional Availability | Asia |

Construction Materials

| | |
|----------------------|---------------|
| Fiber Mode | Multimode |
| Fiber Type | OM3 OM4 |
| Finish | Powder coated |
| Material Type | Steel |

Dimensions

| | |
|---------------|----------------------|
| Depth | 320.00 mm 12.60 in |
| Height | 44.45 mm 1.75 in |
| Width | 482.60 mm 19.00 in |

General Specifications

| | |
|---------------------------------|-------------------|
| Rack Units | 1.0 |
| Shelf Movement | Sliding |
| Body Style | Symmetrical |
| Color | Black |
| Color, front | Black |
| Functionality | Patching |
| Includes | Mounting hardware |
| Interface Feature, front | Standard |
| Interface, front | LC |
| Package Quantity | 1 |
| Rack Type | EIA 19 in |
| Total Ports, quantity | 24 |

Optical Performance

Insertion Loss, maximum 0.30 dB

Return Loss, minimum 20.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

