



FMS Fiber Optic Termination Panel, 1U, 19 in, 12 SC/UPC, singlemode, OS2, black

Product Classification

Portfolio	NETCONNECT®
Product Series	FMS
Product Type	Fiber patch panel
Regional Availability	Asia

Construction Materials

Fiber Mode	Singlemode
Fiber Type	OS2
Finish	Powder coated
Material Type	Steel

Dimensions

Depth	320.00 mm 12.60 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	1.0
Shelf Movement	Sliding
Body Style	Symmetrical
Color	Black
Color, front	Black
Functionality	Patching
Includes	Mounting hardware
Interface Feature, front	Standard
Interface, front	SC
Package Quantity	1
Rack Type	EIA 19 in
Total Ports, quantity	12

Optical Performance

Insertion Loss, maximum 0.30 dB

Return Loss, minimum 45.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

