



OCM5 Fiber Optic Splitter Module, Planar, one 1x64 Splitter, singlemode, LC/APC, symmetrical split ratio, 3.0 m pigtailed

## Product Classification

<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM5
<b>Regional Availability</b>	EMEA

## General Specifications

<b>Distribution Type</b>	1 x 64 splitter
<b>Interface, input</b>	LC
<b>Interface, output</b>	LC
<b>Split Ratio</b>	Symmetrical
<b>Application</b>	For use with FIST cabinets
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Splitting
<b>Interface Feature, input</b>	APC
<b>Interface Feature, output</b>	APC
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Splitter, quantity</b>	1
<b>Technology Type</b>	Planar lightwave circuit (PLC)

## Dimensions

<b>Depth</b>	142.00 mm   5.59 in
<b>Height</b>	154.00 mm   6.06 in
<b>Pigtail length, input</b>	3.00 m   9.84 ft
<b>Pigtail length, output</b>	3.00 m   9.84 ft
<b>Width</b>	16.00 mm   0.63 in

## Mechanical Specifications

<b>Device Type</b>	Standard VAM
<b>Access</b>	Front

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

