

Angled Panel Cover, Black

Product Classification

Portfolio	CommScope®
Product Type	Cover
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	108.20 mm 4.26 in
Height	2.29 mm 0.09 in
Width	424.43 mm 16.71 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Application	For M2400 and M4800 angled panels
Color	Black
Package Quantity	1

Mechanical Specifications

Material Type	Powder-coated steel
----------------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

