



DDM Module for unshielded SL Jacks (4 pcs), Black

Product Classification

| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Module |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|---------------|---------------------|
| Depth | 32.51 mm 1.28 in |
| Height | 41.15 mm 1.62 in |
| Width | 106.68 mm 4.20 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|-------------------------|-------|
| Color | Black |
| Package Quantity | 4 |

Mechanical Specifications

| | |
|----------------------|---|
| Material Type | High-impact, flame retardant, thermoplastic |
|----------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

