

Fiber adapter plate, 1U, unpopulated, for holding up to 4 Quick-Fit modules

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber adapter plate
Regional Availability	Australia/New Zealand EMEA

Dimensions

Depth	39.70 mm 1.56 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Environmental Specifications

Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Color	Black
Package Quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

