



TENIO™ Splice Tray for large closures (CH6 size) for up to 24 heat shrink splice protectors (SMOUV 45 mm)

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays
- Loop-back facility allowing for single circuit uncut looped fiber storage on the splice tray
- Compliant with most splice types and independent of any optical fiber construction

## Product Classification

<b>Product Type</b>	Fiber splice tray
<b>Product Series</b>	TENIO
<b>Regional Availability</b>	EMEA   Latin America

## General Specifications

<b>Color</b>	Gray
<b>Package, quantity</b>	12
<b>Packaging Type</b>	Bag   Carton
<b>Splice Protector Diameter, maximum</b>	5.00 mm   0.20 in
<b>Splice Protector Diameter, minimum</b>	3.50 mm   0.14 in
<b>Splice Protector Length, maximum</b>	45.00 mm   1.77 in
<b>Splice Protector Length, minimum</b>	35.00 mm   1.38 in
<b>Splice Tray Chip Type</b>	Heat shrink
<b>Splice Tray Included, quantity</b>	1
<b>Splices per Tray, quantity</b>	24

## Dimensions

<b>Weight</b>	0.10 kg   0.22 lb
---------------	-------------------

## Mechanical Specifications

<b>Material Type</b>	PBT   PET
<b>Minimum Bend Radius, standard</b>	30.00 mm   1.18 in

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU	<b>Classification</b>	Compliant
---------------	-----------------	-----------------------	-----------

