



MPOptimate® Universal Connectivity Platform (UCP), Micro-Module, 12F, Singlemode, MPO to 6 LC duplex, pairs flipped

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber module
Regional Availability	Asia EMEA

Construction Materials

Fiber Type	OS2
Fiber Mode	Singlemode

Dimensions

Depth	87.00 mm 3.43 in
Height	12.00 mm 0.47 in
Width	83.00 mm 3.27 in

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Black
Adapter Color	Blue
Adapters, quantity, front	6
Application	For use with Universal Connectivity Product (UCP) panels
Body Style	Low-profile Straight orientation
Color, housing	Black
Packaging Type	Bag Carton
Polarity	Pairs, flipped
Interface, rear	MPO
Adapters, quantity, rear	1
Interface Feature, rear	APC
Color, rear	Black

Package Quantity 1

Optical Performance

Insertion Loss, maximum 0.75 dB

Return Loss, minimum 35.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

