

Fiber Optic Panel, 1U, 19 in, fully loaded with 24 aqua LC/UPC MM duplex adapters, black

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	EMEA

## Construction Materials

<b>Fiber Mode</b>	Multimode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## General Specifications

<b>Rack Units</b>	1.0
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Growth Configuration</b>	Fully loaded
<b>Includes</b>	Mounting hardware
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	LC
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Total Ports, quantity</b>	48

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

