

# 244813-M5



CNT-195 CNT® Jumper with interface types N Male and TNC Male, 0.5 m

## Product Classification

<b>Brand</b>	CNT®
<b>Product Series</b>	CNT-195
<b>Product Type</b>	Braided cable assembly

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	TNC Male
<b>Length</b>	0.500 m   1.640 ft
<b>Nominal Size</b>	0.195 in
<b>Specification Sheet Revision Level</b>	A

## Electrical Specifications

<b>DTF, Connector A</b>	-26.00 dB
<b>DTF, Connector B</b>	-28.00 dB

## Jumper Assembly Sample Label

The label contains the following information:

- Batch:** 0123456789
- Manufacturing Date (two digit year and week):** US22 1240
- Manufacturing Plant:** US22
- Product Revision:** /A
- Part Number:** F4-DMDM-2M-D
- Serial Number:** 12US220001242

Additional text on the label includes: COMMSCOPE® Andrew Solutions™, 2 M (6.562 FT), SUREFLEX ASSEMBLY, U.S. PATENT 5802710, Product of UNITED STATES, and a barcode.

## Return Loss/VSWR

### Frequency Band

0–2700 MHz

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

195PNM-CR — Type N Male for CNT-195 braided cable

195PTM — TNC Male for CNT-195 braided cable

CNT-195-FR — CNT-195-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant

CNT-195-P — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.

419001003/10 | CNT-195-P-6G — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.