

C195-BMBM



CNT-195 CNT® Jumper with interface types BNC Male and BNC Male, variable length

Product Classification

Brand	CNT®
Product Series	CNT-195
Product Type	Braided cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	BNC Male
Interface, Connector B	BNC Male
Length	0.000 m 0.000 ft
Nominal Size	0.195 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
----------------	------	------------------

C195-BMBM

700–3000 MHz

1.43

15.00

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

195PBM-CR — BNC Male for CNT-195 braided cable

CNT-195-FR — CNT-195-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant

CNT-195-P — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.

419001003/10 | CNT-195-P-6G — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.