

# C195-NFTM



CNT-195 CNT® Jumper with interface types N Female and TNC Male, variable length

## Product Classification

Brand	CNT®
Product Series	CNT-195
Product Type	Braided cable assembly

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Female
Interface, Connector B	TNC Male
Length	0.000 m   0.000 ft
Nominal Size	0.195 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Jumper Assembly Sample Label

Batch 0123456789 Manufacturing Date (two digit year and week) US22 1240 /A

Manufacturing Plant US22

Product Revision /A

COMMSCOPE® Andrew Solutions™

**F4-DMDM-2M-D** Part Number

2 M (6.562 FT)

SUREFLEX ASSEMBLY

U.S. PATENT 5802710

Product of UNITED STATES

Serial Number 12US220001242

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
----------------	------	------------------

# C195-NFTM

---

700–3000 MHz

1.43

15.00

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

### Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



## Included Products

195PNF-CR — Type N Female for CNT-195 braided cable

195PTM — TNC Male for CNT-195 braided cable

CNT-195-FR — CNT-195-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant

CNT-195-P — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.

419001003/10 | CNT-195-P-6G — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.