

# F1-PNMNM-HF



FSJ1-50A Jumper with interface types N Male and N Male, variable length

## Product Classification

**Product Series** FSJ1-50A  
**Product Type** SureFlex® standard

## General Specifications

**Body Style, Connector A** Straight  
**Body Style, Connector B** Straight  
**Interface, Connector A** N Male  
**Interface, Connector B** N Male  
**Length** 0.000 m | 0.000 ft  
**Nominal Size** 1/4 in  
**Specification Sheet Revision Level** A

## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Jumper Assembly Sample Label

**Batch** 0123456789 **Manufacturing Date** (two digit year and week) 1240 **Manufacturing Plant** US22 **Product Revision** /A

**Part Number** F4-DMDM-2M-D  
2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710  
Product of UNITED STATES

**Serial Number** 12US220001242

COMMSCOPE® Andrew Solutions™

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
10–18000 MHz	1.67	12.00

# F1-PNMNM-HF

---

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
China RoHS SJ/T 11364-2014

### Classification

Compliant by Exemption  
Above Maximum Concentration Value (MCV)



## Included Products

F1PNM-HF — Type N Male for 1/4 in FSJ1-50A cable