

F1-PSMSR-HF



FSJ1-50A Jumper with interface types SMA Male and SMA Male Right Angle, variable length

Product Classification

Product Series FSJ1-50A
Product Type Wireless transmission cable assembly

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Right angle
Interface, Connector A SMA Male
Interface, Connector B SMA Male
Nominal Size 1/4 in
Specification Sheet Revision Level A
Variable Length For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Jumper Assembly Sample Label



Return Loss/VSWR

F1-PSMSR-HF

Frequency Band

10–18000 MHz

VSWR

1.63

Return Loss (dB)

12.00

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



Included Products

F1TSM-HF — SMA Male for 1/4 in FSJ1-50A cable

F1TSR-HF — SMA Male Right Angle for 1/4 in FSJ1-50A cable