

F1-PNMSM-HF



FSJ1-50A Jumper with interface types SMA Male and N Male, variable length

Product Classification

Product Series FSJ1-50A
Product Type SureFlex® standard

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Interface, Connector A SMA Male
Interface, Connector B N Male
Length 0.000 m | 0.000 ft
Nominal Size 1/4 in
Specification Sheet Revision Level A
Variable Length For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Jumper Assembly Sample Label

Batch 0123456789 **Manufacturing Date** (two digit year and week) 1240 **Manufacturing Plant** US22 **Product Revision** /A

Part Number F4-DMDM-2M-D

Serial Number 12US220001242

COMMSCOPE® Andrew Solutions™
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES

F1-PNMSM-HF

Return Loss/VSWR

Frequency Band
10–18000 MHz

VSWR
1.78

Return Loss (dB)
11.00

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



Included Products

F1TSM-HF — SMA Male for 1/4 in FSJ1-50A cable

F1PNM-HF — Type N Male for 1/4 in FSJ1-50A cable