

FLXLCLCAD

LazrSPEED® 550 LC to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 12-Fiber, Plenum

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360 LazrSPEED®
Product Type	Fiber fanout cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM4, LazrSPEED® 550
Total Fibers, quantity	12
Fibers per Subunit, quantity	12
Furcation Color	Aqua

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	3 m 8 ft
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Interface, connector A	LC/UPC
Interface, connector B	LC/UPC
Color, connector A	Beige
Color, connector B	Beige
Construction Type	InstaPATCH® 360 ruggedized fanout, indoor
Cord Configurator	Yes

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
--	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant



Included Products

P-012-MP-5K-F12 (Product Component—not orderable) — LazrSPEED® Plenum MPO Trunk Cable, 12 fiber

- CS-5K-MP (Product Component—not orderable) — LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

460125198 (Product Component—not orderable) — Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode