

C100-PSMSB-12M



CNT-100 CNT® Jumper with interface types SMA Male and SMB Male, 12 m

Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	SMB Male
Length	12.000 m 39.370 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A

Jumper Assembly Sample Label

Batch **Manufacturing Date** (two digit year and week)

Manufacturing Plant **Product Revision**

0123456789 US22 1240 /A

COMMScope Andrew Solutions™

F4-DMDM-2M-D — **Part Number**

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES **12US220001242** — **Serial Number**



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–2000 MHz	1.29	18.00
700–3000 MHz	1.43	15.00

C100-PSMSB-12M

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)



Included Products

100PSBM-CR — SMB Male (= Female pin) for CNT-100 braided cable

100PSM-CR — SMA Male for CNT-100 braided cable

CNT-100-FR — CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket