

C100-SMSM-1M-PA



CNT-100 CNT® Jumper with interface types SMA Male and SMA Male, 1 m

Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	SMA Male
Length	1.000 m 3.281 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A

Jumper Assembly Sample Label

Batch **Manufacturing Date** (two digit year and week)

Manufacturing Plant **Product Revision**

0123456789 US22 1240 /A

COMMScope® Andrew Solutions™

F4-DMDM-2M-D **Part Number**

2 M (6.562 FT)

SUREFLEX ASSEMBLY

U.S. PATENT 5802710

Product of UNITED STATES

12US220001242 **Serial Number**

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–2000 MHz	1.22	20.00
700–3000 MHz	1.29	18.00

C100-SMSM-1M-PA

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products

100PSM-CR — SMA Male for CNT-100 braided cable

CNT-100-FR — CNT-100-FR, CNT@ 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket