



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to dual row standard density outlet, 8 links

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	GigaSPEED X10D®   InstaPATCH® Cu
<b>Product Type</b>	Copper trunk cable assembly
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Cord Length, minimum</b>	5 m   17 ft
<b>Cord Length, maximum</b>	90 m   295 ft

## Electrical Specifications

<b>ANSI/TIA Category</b>	6A
<b>dc Resistance, maximum</b>	0.30 ohm
<b>Safety Voltage Rating</b>	300 V

## Environmental Specifications

<b>Environmental Space</b>	Plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Interface, connector A</b>	Information outlet
<b>Interface, connector B</b>	Information outlet
<b>Interface Feature, connector A</b>	Single row   Standard density
<b>Interface Feature, connector B</b>	Dual row   Standard density

## Mechanical Specifications

<b>Link Count</b>	8
-------------------	---

**Conductor Type** Solid  
**Wiring** T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

MGS600 (Product Component—not orderable) — GigaSPEED X10D® MGS600 Series Information Outlet

2091B 4/23 (Product Component—not orderable) — GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count