



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to dual row OneLink 2x6, 12 links

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Brand</b>                 | GigaSPEED X10D®   InstaPATCH® Cu                                    |
| <b>Product Type</b>          | Copper trunk cable assembly   |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Dimensions

|                             |              |
|-----------------------------|--------------|
| <b>Cord Length, minimum</b> | 2 m   7 ft   |
| <b>Cord Length, maximum</b> | 30 m   98 ft |

## Electrical Specifications

|                               |          |
|-------------------------------|----------|
| <b>ANSI/TIA Category</b>      | 6A       |
| <b>dc Resistance, maximum</b> | 0.30 ohm |
| <b>Safety Voltage Rating</b>  | 300 V    |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Environmental Space</b>   | Plenum                               |
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |

## General Specifications

|                                       |                               |
|---------------------------------------|-------------------------------|
| <b>Cable Type</b>                     | U/UTP (unshielded)            |
| <b>Interface, connector A</b>         | Information outlet            |
| <b>Interface, connector B</b>         | OneLink 2x6                   |
| <b>Interface Feature, connector A</b> | Single row   Standard density |
| <b>Interface Feature, connector B</b> | Standard                      |

## Mechanical Specifications

|                   |    |
|-------------------|----|
| <b>Link Count</b> | 12 |
|-------------------|----|

**Conductor Type** Solid  
**Wiring** T568B

## Regulatory Compliance/Certifications

| Agency          | Classification   |
|-----------------|--|
| RoHS 2011/65/EU | Compliant  |
| ISO 9001:2015   | Designed, manufactured and/or distributed under this quality management system |



## Included Products

MGS600 (Product Component—not orderable) — GigaSPEED X10D® MGS600 Series Information Outlet

2095B 4/24 (Product Component—not orderable) — GigaSPEED X10D® 2095B Category 6A U/UTP Cable, plenum, 4 pair count