



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, dual row standard density outlet to single row standard density outlet, 12 links

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D® InstaPATCH® Cu
Product Type	Copper trunk cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, minimum	5 m 17 ft
Cord Length, maximum	90 m 295 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	Information outlet
Interface, connector B	Information outlet
Interface Feature, connector A	Dual row Standard density
Interface Feature, connector B	Single row Standard density

Mechanical Specifications

Link Count	12
-------------------	----

Conductor Type Solid
Wiring T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

MGS600 (Product Component—not orderable) — GigaSPEED X10D® MGS600 Series Information Outlet

2091B 4/23 (Product Component—not orderable) — GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count