

LazrSPEED® 550 MPO (female) to LC Simplex, InstaPATCH® 360 TM Array Fanout, 12-Fiber, Plenum, 15 ft + 24 in Breakout

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360 LazrSPEED®
Product Type	Fiber fanout cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM4, LazrSPEED® 550
Total Fibers, quantity	12
Jacket Color	Aqua
Fibers per Subunit, quantity	12
Furcation Color	Aqua

Dimensions

Breakout Length	24 in
Cord Length, maximum	5 m 15 ft
Cord Length, minimum	5 m 15 ft
Ordering Note	Fixed length assembly

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	InstaPATCH® 360 array cord
Interface, connector A	MPO-12/UPC Female
Interface, connector B	LC/UPC
Color, connector A	Aqua
Color, connector B	Beige

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
--	---------------------------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860366210 (Product Component—not orderable) — LazrSPEED® Elite MPO Female 12 Fiber Connector, aqua

460125172 (Product Component—not orderable) — Pre-Radiused LC Connector simplex for 1.6 mm Fiber, multimode

P-012-MP-5K-F30AQ (Product Component—not orderable) — LazrSPEED® Plenum MPO Light Duty Patchcord Cable, 12 fiber

- CS-5K-MP (Product Component—not orderable) — LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber