

F1-NMNM-1M-NC



FSJ1-50A Jumper with interface types N Male and N Male, 1 m

Product Classification

Product Series FSJ1-50A
Product Type SureFlex® standard

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Interface, Connector A N Male
Interface, Connector B N Male
Length 1.000 m | 3.281 ft
Nominal Size 1/4 in
Specification Sheet Revision Level A

Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Jumper Assembly Sample Label

Batch 0123456789 **Manufacturing Date** (two digit year and week) 1240 **Manufacturing Plant** US22 **Product Revision** /A

Part Number F4-DMDM-2M-D

Serial Number 12US220001242

COMMSCOPE® Andrew Solutions™
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)
6000–7000 MHz	1.43	15.00	0.92

F1-NMNM-1M-NC

7000–8000 MHz

1.43

15.00

1.10

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)



Included Products

F1PNM-HF — Type N Male for 1/4 in FSJ1-50A cable