

InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to dual row standard density RJ45 plug, 24 links

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D® InstaPATCH® Cu
Product Type	Copper trunk cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, minimum	2 m 7 ft
Cord Length, maximum	30 m 98 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	Information outlet
Interface, connector B	RJ45 plug
Interface Feature, connector A	Single row Standard density
Interface Feature, connector B	Dual row Standard density

Mechanical Specifications

Link Count	24
Conductor Type	Solid
Wiring	T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Included Products

2095B 4/24 (Product Component—not orderable) — GigaSPEED X10D® 2095B Category 6A U/UTP Cable, plenum, 4 pair count

MGS600 (Product Component—not orderable) — GigaSPEED X10D® MGS600 Series Information Outlet