

C100-BNFSR-2M

CNT-100 CNT® Jumper with interface types N Bulkhead Female and SMA Male Right Angle, 2 m



Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

General Specifications

Body Style, Connector A	Bulkhead
Body Style, Connector B	Right angle
Interface, Connector A	N Female
Interface, Connector B	SMA Male
Length	2.000 m 6.562 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A

Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE® Andrew Solutions™

F4-DMDM-2M-D Part Number

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES

12US220001242 Serial Number

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
----------------	------	------------------

C100-BNFSR-2M

700–3000 MHz

1.33

17.00

Included Products

CNT-100-FR — CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket